

Specification Sheet

Part Number: 151-00077



Clip can be installed by hand – no need for hardware or tools.

Design provides low insertion and high extraction force, for simple, secure performance.

Clip keeps bundle away from areas that could cause damage due to rubbing.

Standoff Bundling Clip, 2.0" Long, 0.03 - 0.06" Panel Thickness, PA66HS, Black, 100/pkg

Article Number	151-00077
----------------	-----------

Type	CH20D6
------	--------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	Bundling clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties. The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standard bundling clips are available as well as standoff and stud mount versions.
---------------------	--

Short Description	Standoff Bundling Clip, 2.0" Long, 0.03 - 0.06" Panel Thickness, PA66HS, Black, 100/pkg
-------------------	---

Global Part Name	CH20D6-PA66HS-BK
------------------	------------------

Length L (Imperial)	2.0
---------------------	-----

Length L (Metric)	50.0
-------------------	------

Offset Length (Imperial)	0.79
--------------------------	------

Offset Length (Metric)	20.0
------------------------	------

Fixation Method	Arrowhead
-----------------	-----------

Height H (Imperial)	0.3
---------------------	-----

Height H (Metric)	7.62
-------------------	------

Panel Thickness Min (Imperial)	0.02
--------------------------------	------

Panel Thickness Max (Imperial)	0.06
--------------------------------	------

Panel Thickness Min (Metric)	0.6
------------------------------	-----

Panel Thickness Max (Metric)	1.4
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.25 - 0.28
-------------------------------------	-------------

Mounting Hole Diameter D (Metric)	6.4 - 7.0 mm
-----------------------------------	--------------

Mounting Hole Diameter D Min (Imperial)	0.25
---	------

Mounting Hole Diameter D Max (Imperial)	0.28
---	------

Mounting Hole Diameter D Max (Metric)	7.0
---------------------------------------	-----

Material	Polyamide 6.6 heat stabilized (PA66HS)
----------	--

Material Shortcut	PA66HS
-------------------	--------

Flammability	UL 94 V-2
--------------	-----------

UV Resistant (Yes/No)	No
-----------------------	----

Operating Temperature	-40°F to +221°F (-40°C to +105°C)
-----------------------	-----------------------------------

Reach Compliant (Article 33)	Yes
------------------------------	-----

ROHS Compliant	Yes
----------------	-----

Package Quantity (Imperial)	100
-----------------------------	-----

Package Quantity (Metric)	100
---------------------------	-----

Customs Number	3926909988
----------------	------------

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-00077](#)