

Specification Sheet

Part Number: 151-00080



Clip can be installed by hand – no need for hardware or tools.

Design provides low insertion and high extraction force, for simple, secure performance.

Clip keeps bundle away from areas that could cause damage due to rubbing.

Standoff Bundling Clip, 1.7" Long, 0.25 - 0.28" Panel Thickness, PA66HS, Black, 500/pkg

Article Number	151-00080
----------------	-----------

Type	COW30DP7
------	----------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	Bundling clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties. The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standard bundling clips are available as well as standoff and stud mount versions.
---------------------	--

Short Description	Standoff Bundling Clip, 1.7" Long, 0.25 - 0.28" Panel Thickness, PA66HS, Black, 500/pkg
-------------------	---

Global Part Name	COW30DP7-PA66HS-BK
Length L (Imperial)	1.7
Length L (Metric)	43.18
Offset Length (Imperial)	1.18
Offset Length (Metric)	30.0
Fixation Method	Fir Tree
Width W (Imperial)	1.7
Width W (Metric)	42.0
Height H (Imperial)	0.26
Height H (Metric)	6.6
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.18
Panel Thickness Min (Metric)	0.8
Panel Thickness Max (Metric)	4.5
Mounting Hole Diameter D (Imperial)	0.24 - 0.26 (hexagonal) ";0.25 - 0.28
Mounting Hole Diameter D (Metric)	6.3 - 7.0 mm 6.1 - 6.6 mm (hexagonal)

Mounting Hole Diameter D Min (Imperial) 0.24

Mounting Hole Diameter D Max (Imperial) 0.28

Mounting Hole Diameter D Max (Metric) 7.0

Material Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut PA66HS

Flammability UL 94 V-2

UV Resistant (Yes/No) No

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 500

Package Quantity (Metric) 500

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-00080](#)