

Specification Sheet

Part Number: TM1SF10M4

 Product Image

Push Mounts, when used with standard cable ties, provide a permanent bundling solution.
The low profile style head is ideal for space constrained areas and is easily inserted through a pre-drilled hole.

Push-Button Cable Tie Mount, .25" Hole Dia, .13" Max Panel, .2" Max Tie Width, PA66, White, 1000/pkg

Article Number	151-00328
Type	TM1SF
Color	White (WH)
Quantity Per	bag
Product Description	HellermannTyton push mounts are used with our standard cable ties and offer a permanent bundling solution for quick installation by pushing the mount through a pre-drilled hole. The low profile head is suitable in space constrained areas.
Short Description	Push-Button Cable Tie Mount, .25" Hole Dia, .13" Max Panel, .2" Max Tie Width, PA66, White, 1000/pkg
Global Part Name	TM1SF-PA66-WH

Length L (Imperial)	0.62
Length L (Metric)	15.75
Fixation Method	with Arrowhead / Push Mount (Mounts)
Width W (Imperial)	0.4
Width W (Metric)	10.2
Cable Ties	T18 - T50
Height H (Imperial)	.18
Height H (Metric)	4.60
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.0
Panel Thickness Min (Imperial)	0.134
Panel Thickness Max (Imperial)	0.13
Panel Thickness Min (Metric)	3.4
Panel Thickness Max (Metric)	3.4
Mounting Hole Diameter D (Imperial)	0.25
Mounting Hole Diameter D (Metric)	6.35 mm

Mounting Hole Diameter D Max (Metric) 6.35

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL 94 V-2

Operating Temperature -40°F to +185°F (-40°C to +85°C)

ROHS Compliant Yes

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes

Package Quantity (Imperial) 1000

Package Quantity (Metric) 1000

Customs Number 3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[TM1SF10M4](#)