

Specification Sheet

Part Number: 151-00378



Clips can be connected to each other to create a chain of cable harnesses.

Secures firmly to surfaces to eliminate moisture and corrosion.

Quick and easy installation ideal for the production environment.

Automatic Harness Clip, Connectable, 1.1" Bundle Max, PA66HIRHS, Black, 500/pkg

Article Number	151-00378
----------------	-----------

Type	IAHC3AH
------	---------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	Automatic Harness Clips offer a simple and secure method of attaching cables to panels and other surfaces. When the cable is pushed inside, it automatically activates the locking features which causes it to close. These are also connectable which allows for multiple cables to be positioned next to each other. These come in various sizes to fit different bundle diameters.
---------------------	---

Short Description	Automatic Harness Clip, Connectable, 1.1" Bundle Max, PA66HIRHS, Black, 500/pkg
-------------------	---

Global Part Name	IAHC3AH-PA66HIRHS-BK
------------------	----------------------

Length L (Imperial)	1.6
---------------------	-----

Length L (Metric)	40.0
-------------------	------

Width W (Imperial)	0.4
--------------------	-----

Width W (Metric)	13.5
------------------	------

Bundle Diameter Min (Metric)	19.0
------------------------------	------

Bundle Diameter Max (Metric)	28.0
------------------------------	------

Height H (Imperial)	2.5
---------------------	-----

Height H (Metric)	64.5
-------------------	------

Panel Thickness Min (Imperial)	0.04
--------------------------------	------

Panel Thickness Max (Imperial)	0.03
--------------------------------	------

Panel Thickness Min (Metric)	0.7
------------------------------	-----

Panel Thickness Max (Metric)	2.7
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.24 - 0.26
-------------------------------------	-------------

Mounting Hole Diameter D (Metric)	6.2 - 6.7 mm
-----------------------------------	--------------

Mounting Hole Diameter D Max (Metric)	6.7
---------------------------------------	-----

Disc Diameter (Metric)	24.0
Disc Diameter (Imperial)	0.94
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-00378](#)