

Specification Sheet

Part Number: 151-00677



Head design contains clamping rails to provide full circumferential compression around bundles.

Bent tail allows for quick insertion into head.

Conn. Clip w/Fir Tree, 0.76-5.75mm Panel Thick., 6.25-6.75mm Hole Dia., PA66HIRHS, Natural, 5000/ctn

Article Number	151-00677
----------------	-----------

Type	CC08
------	------

Color	Natural (NA)
-------	--------------

Quantity Per	carton
--------------	--------

Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
---------------------	---

Short Description	Conn. Clip w/Fir Tree, 0.76-5.75mm Panel Thick., 6.25-6.75mm Hole Dia., PA66HIRHS, Natural, 5000/ctn
-------------------	--

Global Part Name	CC08-PA66HIRHS-NA
-------------------------	-------------------

Length L (Imperial)	0.99
----------------------------	------

Length L (Metric)	25.2
--------------------------	------

Fixation Method	Fir Tree
------------------------	----------

Width W (Imperial)	0.78
---------------------------	------

Width W (Metric)	19.81
-------------------------	-------

Height H (Imperial)	0.81
----------------------------	------

Height H (Metric)	20.55
--------------------------	-------

Panel Thickness Min (Imperial)	0.03
---------------------------------------	------

Panel Thickness Max (Imperial)	0.23
---------------------------------------	------

Panel Thickness Min (Metric)	0.7
-------------------------------------	-----

Panel Thickness Max (Metric)	5.75
-------------------------------------	------

Mounting Hole Diameter D (Imperial)	0.08 x 0.26
--	-------------

Mounting Hole Diameter D (Metric)	6.25 - 6.75 mm
--	----------------

Mounting Hole Diameter D Min (Imperial)	0.08
--	------

Mounting Hole Diameter D Max (Imperial)	0.26
--	------

Mounting Hole Diameter D Max (Metric) 6.75

Material Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut PA66HIRHS

Operating Temperature -40°F to +230°F (-40°C to +110°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 5000

Package Quantity (Metric) 5000

Customs Number 3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-00677](#)