

Specification Sheet

Part Number: 151-01108



HellermannTyton Connector Clips provide a single method to mount connectors to various surfaces in a variety of applications.

Highly engineered designs feature anti-rattle discs, anti-rotation oval fir trees and clamps for mounting on edges.

An assortment of Connector Clips is available to fit the variety of connector slot designs made by most of the largest global connector manufacturers.

Connector Clip with Oval Fir Tree, 0.6-6.0mm Panel Thick, 6.2-13.0mm Hole Dia, PA66HIRHSUV, Black, 5000/ctn

Article Number	151-01108
----------------	-----------

Type	CCOVAL2
------	---------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
---------------------	---

Short Description	Connector Clip with Oval Fir Tree, 0.6-6.0mm Panel Thick, 6.2-13.0mm Hole Dia, PA66HIRHSUV, Black, 5000/ctn
-------------------	---

Global Part Name	CCOVAL2-PA66HIRHSUV-BK
Length L (Imperial)	1.14
Length L (Metric)	29.0
Fixation Method	Fir Tree for oval holes
Variant	6.2 x 12.2 mm 6.5 x 12.5 mm 6.5 x 13.0 mm 7.0 x 12.0 mm
Width W (Imperial)	0.69
Width W (Metric)	17.6
Height H (Imperial)	0.80
Height H (Metric)	22.35
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.24
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.24 x 0.48 " 0.26 x 0.50 " 0.26 x 0.51 " 0.28 x 0.47
Mounting Hole Diameter D (Metric)	6.2 x 12.2 mm 6.5 x 13.0 mm 6.5 x 12.5 mm 7.0 x 12.0 mm
Mounting Hole Diameter D Min (Imperial)	0.24

Mounting Hole Diameter D Max (Imperial)	0.24
---	------

Mounting Hole Diameter D Max (Metric)	6.2
---------------------------------------	-----

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
----------	--

Material Shortcut	PA66HIRHSUV
-------------------	-------------

UV Resistant (Yes/No)	Yes
-----------------------	-----

Operating Temperature	-40°F to +221°F (-40°C to +105°C)
-----------------------	-----------------------------------

Reach Compliant (Article 33)	Yes
------------------------------	-----

ROHS Compliant	Yes
----------------	-----

Package Quantity (Imperial)	5000
-----------------------------	------

Package Quantity (Metric)	5000
---------------------------	------

Customs Number	3926909988
----------------	------------

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-01108](#)