

Specification Sheet

Part Number: 151-01109

The 90-degree configuration of this mini channel creates a solution for routing a wire harness around a corner.

Design allows the mini channel to be used with a wide range of panel thicknesses and hole diameters.



Disc prevents rattling in high-vibration applications and protects against leakage and debris.

Mini Channel, 1.38" Long, 90° Angle, Arrowhead, PA66HIRHSUV, Black, 4000/pkg

Article Number	151-01109
----------------	-----------

Type	BC90AH2
------	---------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	HellermannTyton's Bundling Clips create a solution that allows the harness to be routed around a corner, and fixated into the panel at this location.
---------------------	---

Short Description	Mini Channel, 1.38" Long, 90° Angle, Arrowhead, PA66HIRHSUV, Black, 4000/pkg
-------------------	--

Global Part Name	BC90AH2-PA66HIRHSUV-BK
------------------	------------------------

Length L (Imperial)	0.98
Length L (Metric)	25.0
Fixation Method	Arrowhead
Width W (Imperial)	0.06
Width W (Metric)	1.5
Height H (Imperial)	0.93
Height H (Metric)	23.6
Diameter D (Imperial)	0.50
Diameter D (Metric)	12.58
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.06
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	1.5
Mounting Hole Diameter D (Imperial)	0.24 - 0.27
Mounting Hole Diameter D (Metric)	6.2 - 6.8 mm
Mounting Hole Diameter D Min (Imperial)	0.24

Mounting Hole Diameter D Max (Imperial)	0.27
Mounting Hole Diameter D Max (Metric)	6.8
Disc Diameter (Metric)	12.58
Disc Diameter (Imperial)	0.50
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	4000
Package Quantity (Metric)	4000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-01109](#)