

Specification Sheet

Part Number: 151-01122



Separates bundles to help prevent chafing and wear.

Single bundles can be mounted on top of the mount, or two bundles can be separated using the two side saddles; giving the mount versatility.

Low profile design allows mount to be placed in areas where space is limited.

Low Profile Screw Mount, 1.8 x 0.98", 0.25" Hole, PA66HIRHSUV, Black, 500/pkg

Article Number	151-01122
----------------	-----------

Type	LPM25
------	-------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	Low Profile Mounts secure bundles close to mounting surfaces, making them ideal for applications where bundle mounting space is limited. These are secured with a .25" mechanical fastener, and have a counter bore for easy access with a socket which can be torqued up to 100 in/lbs. The mount accommodates cable ties up to .5" in width.
---------------------	--

Short Description	Low Profile Screw Mount, 1.8 x 0.98", 0.25" Hole, PA66HIRHSUV, Black, 500/pkg
-------------------	---

Global Part Name	LPM25-PA66HIRHSUV-BK
------------------	----------------------

Length L (Imperial)	1.8
Length L (Metric)	45.1
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	0.98
Width W (Metric)	24.9
Cable Ties	T50 - T250
Height H (Imperial)	0.66
Height H (Metric)	16.7
Cable Tie Width Max (Imperial)	0.53
Cable Tie Width Max (Metric)	13.5
Mounting Hole Diameter D (Imperial)	0.25
Mounting Hole Diameter D (Metric)	6.7 mm
Mounting Hole Diameter D Max (Metric)	6.7
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-01122](#)