

Specification Sheet

Part Number: 151-01231



Design provides quick and easy assembly.

Isolator mount dampens harmful vibrations on bundles

Material is durable, chemical and abrasion resistant, and remains flexible in low temperatures.

Heavy Duty Hinge Clamp, 0.59" Max Diameter, PA46, Black, 250/pkg

Article Number	151-01231
----------------	-----------

Type	HDHC59
------	--------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	These clamps separate multiple bundles and secure them to any surface with a 6.8 mm stud or bolt. The one-piece hinged design snaps together to keep bundles such as tubing or battery cables separated. The mounting hole features two pawls for easy preinstallation on a threaded fastener prior to securing with a mechanical fastener.
---------------------	---

Short Description	Heavy Duty Hinge Clamp, 0.59" Max Diameter, PA46, Black, 250/pkg
-------------------	--

Global Part Name	HDHC59-PA46-BK
------------------	----------------

Length L (Imperial)	7.32
Length L (Metric)	186.0
Width W (Imperial)	0.57
Width W (Metric)	14.5
Bundle Diameter Max (Imperial)	0.59
Bundle Diameter Max (Metric)	15.0
Height H (Imperial)	1.22
Height H (Metric)	30.9
Mounting Hole Diameter D (Imperial)	0.27
Mounting Hole Diameter D (Metric)	6.8 mm

Material Polyamide 4.6 (PA46)

Material Shortcut PA46

UV Resistant (Yes/No) No

Use Conditions For Indoor Use Only

Operating Temperature -40°F to +266°F (-40°C to +130°C)

Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	250
Package Quantity (Metric)	250
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-01231](#)