

Specification Sheet

Part Number: 151-01310



Fir Tree demonstrates easy insertion with high extraction resistance in 65 +/- 0.4 mm hole
C-clip design allows for multiple uses, from hoses and tubes to harnesses and cables

Dual FT6 Docking Clip, 12-15mm with 6.5mm Fir Tree, PA66HIRHSUV, Black, 2000/pkg

Article Number	151-01310
-----------------------	-----------

Type	DUALFT6DOCK
-------------	-------------

Color	Black (BK)
--------------	------------

Quantity Per	carton
---------------------	--------

Product Description	HellermannTyton connector clips for oval holes are mounted simply by pushing them onto the corresponding clip. The clips provide a wide range of mounting options with anti-rattle and anti-rotation features. The fir tree locks into place when inserted into the hole palpably and ensures a secure fixing at all times. Dual routing clip provides a secure fit for two routings between 12 - 15 mm diameter.
----------------------------	---

Short Description	Dual FT6 Docking Clip, 12-15mm with 6.5mm Fir Tree, PA66HIRHSUV, Black, 2000/pkg
--------------------------	--

Global Part Name	DUALFT6DOCK-PA66HIRHSUV-BK
------------------	----------------------------

Length L (Imperial)	2.04
---------------------	------

Length L (Metric)	51.8
-------------------	------

Fixation Method	Fir Tree
-----------------	----------

Width W (Imperial)	0.66
--------------------	------

Width W (Metric)	16.66
------------------	-------

Height H (Imperial)	1.36
---------------------	------

Height H (Metric)	34.63
-------------------	-------

Nominal Diameter (Metric)	15.5
---------------------------	------

Panel Thickness Min (Imperial)	0.02
--------------------------------	------

Panel Thickness Max (Imperial)	0.24
--------------------------------	------

Panel Thickness Min (Metric)	0.6
------------------------------	-----

Panel Thickness Max (Metric)	6.0
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.26
-------------------------------------	------

Mounting Hole Diameter D (Metric)	6.5 mm
-----------------------------------	--------

Mounting Hole Diameter D Max (Metric)	6.9
---------------------------------------	-----

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-01310](#)