

Specification Sheet

Part Number: 151-01317



Easy assembly without the need of a tool.
Disc covers mounting hole and minimizes ingress of dust, dirt and water.
Standard geometry fits common 6.5 mm hole size.

Push Pin, Mounting Hole Dia. 6.5mm, PA66HIRHSUV, Black, 5000/carton

Article Number	151-01317
-----------------------	-----------

Type	FT6.5 Plug
-------------	------------

Color	Black (BK)
--------------	------------

Quantity Per	carton
---------------------	--------

Product Description	Developed especially for the automotive industry in applications including trunks, doors, wheel housings and dash panels.
----------------------------	---

Short Description	Push Pin, Mounting Hole Dia. 6.5mm, PA66HIRHSUV, Black, 5000/carton
--------------------------	---

Global Part Name	FT6.5 Plug-PA66HIRHS-BK
-------------------------	-------------------------

Minimum Tensile Strength (Imperial)	25
Minimum Tensile Strength (Metric)	110
Length L (Imperial)	0.76
Length L (Metric)	18.60
Fixation Method	Fir Tree
Width W (Imperial)	0.62
Width W (Metric)	15.7
Height H (Imperial)	0.48
Height H (Metric)	12.5
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.24
Panel Thickness Min (Metric)	0.60
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.24 - 0.27
Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.27

Mounting Hole Diameter D Max (Metric)	6.9
Disc Diameter (Metric)	18.6
Disc Diameter (Imperial)	0.73
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Package Quantity (Imperial)	5000
Package Quantity (Metric)	5000
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-01317](#)