

Specification Sheet

Part Number: 151-01870

HellermannTyton connector clips provide a simple and easy method for mounting connectors to a mounting surface in a variety of applications. Detailed designs include anti-rattle disc features, anti-rotation oval fir trees, and clamps for mounting on edges.

HellermannTyton offers an assortment of connector clips that are available for a variety of connector slot designs found on most of the largest global connector manufacturers.



Article Number	151-01870
Type	YCCKSFT6.5-PT1.7-2.3
Color	Black (BK)
Quantity Per	bag
Product Description	HellermannTyton connector clips, for oval holes, are mounted simply by pushing them onto the corresponding clip. The clips provide a wide range of mounting options with anti-rattle and anti-rotation features. The fir tree locks into place when inserted into the hole palpably and ensures a secure fixing at all times.
Short Description	Connector Clip w/Arrowhead, 1.7 - 2.3 mm Panel Thickness, 6.3 - 6.7 mm Hole Dia, PA66HIRHS, Black, 500/pkg

Global Part Name	YCCKSFT6.5-PT1.7-2.3-PA66HIRHS-BK
Length L (Metric)	27.0
Fixation Method	Arrowhead (Small Mount)
Width W (Metric)	16.0
Height H (Metric)	11.9
Panel Thickness Min (Metric)	1.7
Panel Thickness Max (Metric)	2.3
Mounting Hole Diameter D (Metric)	6.3 - 6.7 mm
Mounting Hole Diameter D Max (Metric)	6.7
Disc Diameter (Metric)	16.0
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
----------------	-----

Package Quantity (Imperial)	500
-----------------------------	-----

Package Quantity (Metric)	500
---------------------------	-----

Customs Number	3926909988
----------------	------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-01870](#)