

Specification Sheet

Part Number: 151-02051

HellermannTyton's 4x oval fir tree prevents bundle rotation while providing best-in-class installation and extraction resistance for four common oval sizes.
Angled connector clip allows for clearance from obstructions and sheet metal contours.



Connector clip design meets USCAR EWCAP-005-11 clip slot specifications, assuring compliance.

Connector Clip, 6.2–13.0mm Hole Dia., PA66HIRHSUV, Black, 5000/carton

Article Number	151-02051
Type	CC22
Color	Black (BK)
Quantity Per	carton
Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Short Description	Connector Clip, 6.2–13.0mm Hole Dia., PA66HIRHSUV, Black, 5000/carton
Global Part Name	CC22-PA66HIRHSUV-BK
Length L (Imperial)	1.01
Length L (Metric)	25.71
Fixation Method	Fir Tree
Width W (Imperial)	0.69
Width W (Metric)	17.53
Height H (Metric)	26.0
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.27
Panel Thickness Min (Metric)	0.51
Panel Thickness Max (Metric)	6.75
Mounting Hole Diameter D (Imperial)	0.24 x 0.48 " 0.26 x 0.50 " 0.26 x 0.51 " 0.28 x 0.47
Mounting Hole Diameter D (Metric)	6.5 x 13.0 mm 6.2 x 12.2 mm 6.5 x 12.5 mm 7.0 x 12.0 mm
Mounting Hole Diameter D Min (Imperial)	0.24

Mounting Hole Diameter D Max (Imperial) 0.51

Mounting Hole Diameter D Max (Metric) 13.0

Material Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut PA66HIRHSUV

Flammability UL 94 HB

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) No

ROHS Compliant Yes

Package Quantity (Imperial) 5000

Package Quantity (Metric) 5000

Customs Number 3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-02051](#)