

Specification Sheet

Part Number: 151-02206

Non-rotating fir tree provides easy insertion with high extraction resistance for 8x14 mm and 8x15 mm oval holes.

Meets installation and extraction requirements of SAE/USCAR-2, for easy installation with reliable performance.

Short fir tree avoids obstructions on opposite side of panel.

Connector clip design meets USCAR EWCAP-005-11 clip slot specifications, assuring compliance.



Connector Clip, 8.0–15.0mm Hole Dia., PA66HIRHSUV, Black, 5000/carton

Article Number	151-02206
----------------	-----------

Type	CC16R
------	-------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
---------------------	---

Short Description	Connector Clip, 8.0–15.0mm Hole Dia., PA66HIRHSUV, Black, 5000/carton
Global Part Name	CC16R-PA66HIRHSUV-BK
Length L (Imperial)	1.18
Length L (Metric)	30.0
Fixation Method	Fir Tree
Width W (Imperial)	0.72
Width W (Metric)	18.2
Height H (Imperial)	0.92
Height H (Metric)	23.4
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.31
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.33 " x 0.55 " 0.31 " x 0.59
Mounting Hole Diameter D (Metric)	8.0 x 15.0 mm 8.0 x 14.0 mm

Mounting Hole Diameter D Min (Imperial) 0.31

Mounting Hole Diameter D Max (Imperial) 0.59

Material Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut PA66HIRHSUV

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 5000

Package Quantity (Metric) 5000

Customs Number 3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-02206](#)