

Specification Sheet

Part Number: 151-02655



5.9 " long straight channel allows for easy bundling.
Polypropylene material provides good chemical and heat resistance.
Design protects bundles against abrasion and other environmental factors.

Mini Channel, 5.9" Long, 180° Angle, Straight, PPT20, Black, 500/pkg

Article Number	151-02655
Type	150STRTCHNL
Color	Black (BK)
Quantity Per	bag
Product Description	HellermannTyton Mini Channels provide protection and configurable routing in a cost-effective wire management solution. The variety of sizes and configurations enables engineers and installers to create optimum routing scenarios. Mini channels replace engineered channels that are costly to design and develop.
Short Description	Mini Channel, 5.9" Long, 180° Angle, Straight, PPT20, Black, 500/pkg
Global Part Name	150STRTCHNL-PPTD20-BK

Length L (Imperial)	5.9
Length L (Metric)	150.0
Width W (Imperial)	0.06
Width W (Metric)	1.5
Height H (Imperial)	0.60
Height H (Metric)	15.0
Mounting Hole Diameter D (Imperial)	0.24 " - 0.27
Mounting Hole Diameter D (Metric)	6.2 - 6.8 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.65

Material Polypropylene 20% Talkum (PPTD20)

Material Shortcut PPTD20

Flammability UL 94 HB

Operating Temperature	-40°F to +149°F (-40°C to +65°C)
------------------------------	----------------------------------

Package Quantity (Imperial)	500
------------------------------------	-----

Package Quantity (Metric)	500
----------------------------------	-----

Customs Number	3926909988
-----------------------	------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-02655](#)