

Specification Sheet

Part Number: 151-02802



Connector clip designed to meet USCAR EWCAP-005-7 clip slot specifications, assuring compliance.

Meets installation and extraction requirements of SAE/USCAR-2, for ease of insertion and reliable performance.

Offset design allows for clearance from obstructions and sheet metal contours.

Article Number	151-02802
----------------	-----------

Type	CCM10SO28R
------	------------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
---------------------	---

Short Description	Conn. Clip w/Offset M10 Thread Stud Mount, 28mm Offset, 7mm Conn Clip, PA66HIRHSUV, BK, 2000/ctn
-------------------	--

Global Part Name	CCM10SO28R-PA66HIRHSUV-BK
Length L (Imperial)	1.53
Length L (Metric)	38.9
Offset Length (Imperial)	1.102
Offset Length (Metric)	28.0
Variant	M10 Threaded Stud 28 mm Offset
Height H (Imperial)	0.736
Height H (Metric)	18.7
Stud Diameter (Metric)	M10
Stud Diamater (Imperial)	0.3937
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	No

ROHS Compliant	Yes
-----------------------	-----

Package Quantity (Imperial)	2000
------------------------------------	------

Package Quantity (Metric)	2000
----------------------------------	------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-02802](#)