

Specification Sheet

Part Number: 151-02981



- Can be easily assembled to convoluted tubing and reliably remain in position
- Internal rib prevents movement or rattling
- Multiple bracket configurations mount to a variety of surfaces
- Releasable to allow for maintenance

Conduit Clamps, Size 16, Mounting Hole 6.5 mm, Offset 60.5 mm, PA66HIRHS, Black, 50/pkg

Article Number	151-02981
Type	CDC16S60.5M6
Color	Black (BK)
Quantity Per	carton
Product Description	The Convoluted Tubing Clamp provides a quick method for securing and routing convoluted tubing. The clamp has an internal rib that prevents movement of the tubing and rattling. Living hinge allows placement and positioning of tubing before locking in place. Convoluted tubing clamps are available in various tubing diameters. Choose from arrowhead, fir tree, bundling clip, bracket and dual clamp configurations.
Short Description	Conduit Clamps, Size 16, Mounting Hole 6.5 mm, Offset 60.5 mm, PA66HIRHS, Black, 50/pkg

Global Part Name	CDC16S60.5M6-PA66HIRHS-BK
-------------------------	---------------------------

Length L (Imperial)	3.48
----------------------------	------

Length L (Metric)	88.3
--------------------------	------

Variant	Clamps
----------------	--------

Width W (Imperial)	0.9
---------------------------	-----

Width W (Metric)	23
-------------------------	----

Bundle Diameter Max (Imperial)	0.63
---------------------------------------	------

Bundle Diameter Max (Metric)	16.0
-------------------------------------	------

Height H (Imperial)	2.44
----------------------------	------

Height H (Metric)	61.9
--------------------------	------

Inner Diameter D (Imperial)	0.95
------------------------------------	------

Inner Diameter D (Metric)	24.2
----------------------------------	------

Diameter D (Imperial)	0.69
------------------------------	------

Diameter D (Metric)	17.4
----------------------------	------

Nominal Diameter (Imperial)	0.63
------------------------------------	------

Nominal Diameter (Metric)	16.0
----------------------------------	------

Mounting Hole Diameter D (Imperial)	0.26
Mounting Hole Diameter D (Metric)	6.5 mm
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
Halogen Free	No
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-02981](#)