

Specification Sheet

Part Number: 151-04018



No drilling or extra hardware required – just secure to steel surface.

Magnetic mounts are reliable even in debris, dirt, and oil.

Use for permanent mounting or as a temporary installation tool.

Reuse and reposition capabilities allow for a flexible mounting solution.

Easily remove without residue.

Magnetic Cable Tie Mount, Grip Tie, 1.02" Dia, Neodymium Magnet/POM/ST, 15lb Pull Force, Blk, 100/bg

Article Number	151-04018
Type	MAGCTM15H
Color	Black (BK)
Quantity Per	bag

Product Description	Magnetic cable tie mounts route bundles by securing to steel surfaces without the need for a mounting hole. Simply attach the wire bundle to the mount with a cable tie and position it onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. The mounts are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts. Magnetic cable tie mounts can be paired with HellermannTyton grip ties.
Short Description	Magnetic Cable Tie Mount, Grip Tie, 1.02" Dia, Neodymium Magnet/POM/ST, 15lb Pull Force, Blk, 100/bg
Global Part Name	MAGCTM15H-NDFEB39/POM/ST-BK
Fixation Method	Magnet
Height H (Imperial)	0.56
Height H (Metric)	14.4
Diameter D (Imperial)	1.02
Diameter D (Metric)	26
Cable Tie Width Max (Imperial)	0.75
Cable Tie Width Max (Metric)	19.1
Material	Polyacetal (POM) Steel (ST) Neodymium alloy 39M (NDFEB39)

Material Shortcut	NDFEB39 ST POM
Halogen Free	Yes
Plenum Rating	AH-2
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Listed (US and Canada)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	8505110070

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-04018](#)