

Specification Sheet

Part Number: 156-00069

Friction tab inside the fir tree allows the tie to sit in mount without falling out prior to installation.

Fir tree provides low insertion effort yet demonstrates high extraction resistance.

Disc feature prevents rattling in high-vibration applications and protects against debris ingress.



Article Number 156-00069

Type WSIFT9A

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.

Short Description Heavy Duty Cable Tie/Fir Tree Mount, 15" x .3", .03"-.25" Panel Thick, PA66HIRHSUV, Black, 100/pkg

Global Part Name

WSIFT9A-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial) 120.0

Minimum Tensile Strength (Metric) 535.0

Length L (Imperial) 15.0

Length L (Metric) 387.0

Fixation Method Fir Tree

Identification Plate Position none

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.3

Width W (Metric) 7.6

Bundle Diameter Min (Imperial) 0.38

Bundle Diameter Min (Metric) 9.5

Bundle Diameter Max (Imperial) 3.25

Bundle Diameter Max (Metric) 82.5

Height H (Imperial) .75

Height H (Metric)	19.10
Panel Thickness Min (Imperial)	0.039
Panel Thickness Max (Imperial)	0.256
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	6.5
Mounting Hole Diameter D (Imperial)	0.34 - 0.36
Mounting Hole Diameter D (Metric)	8.7 - 9.2 mm
Mounting Hole Diameter D Min (Imperial)	0.34
Mounting Hole Diameter D Max (Imperial)	0.36
Mounting Hole Diameter D Max (Metric)	9.25
Disc Diameter (Metric)	21.6
Disc Diameter (Imperial)	0.85
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB

Operating Temperature -40°F to +221°F (-40°C to +105°C)

ROHS Compliant Yes

Package Quantity (Imperial) 100

Package Quantity (Metric) 100

Customs Number 3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-00069](#)