

Specification Sheet

Part Number: 156-00408

Tie/mount combination eliminates the need to carry multiple sizes of fixed bundle diameter clamps.

Can be assembled directly on harnesses or on production line for installation versatility.

Available in PA66 heat-stabilized or PA46, they are suitable for various temperature grades.

Designed to meet strict automotive standards, they are well adapted to vibration and lateral forces.

Metal inserts withstand high-torque tightening.

H-design allows full contact with harnesses or other tubes and hoses.

Mainly adapted to T120R and T120S cable ties but can also be assembled with smallest sizes.



2-Piece Cable Tie/Screw Mount, 15" Long, M8 Hole, 120lb, PA66HIRHS, Black, 100/bg

Article Number	156-00408
Type	T120RHDM8
Color	Black (BK)
Quantity Per	bag

Product Description	These cable tie mounts attach with a screw or bolt to an existing hole, or secure to a stud with a nut. They provide an attachment point for securing and routing a single bundle and deliver the highest level of fastening strength for critical cable security.
Short Description	2-Piece Cable Tie/Screw Mount, 15" Long, M8 Hole, 120lb, PA66HIRHS, Black, 100/bg
Global Part Name	T120RHDM8-PA66HIRHS-BK
Minimum Tensile Strength (Imperial)	120
Minimum Tensile Strength (Metric)	535
Length L (Imperial)	15.0
Length L (Metric)	390.0
Fixation Method	Screw Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.30
Width W (Metric)	7.6
Bundle Diameter Min (Imperial)	0.59

Bundle Diameter Min (Metric)	15.0
Bundle Diameter Max (Imperial)	3.937
Bundle Diameter Max (Metric)	105.0
Bundle Diameter 1st Loop Max (Imperial)	3.937
Bundle Diameter 1st Loop Max (Metric)	100
Thickness T (Imperial)	0.07
Thickness T (Metric)	1.8
Height H (Imperial)	0.61
Height H (Metric)	16.0
Mounting Hole Diameter D (Imperial)	0.33
Mounting Hole Diameter D (Metric)	8.4 mm
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Material Cable Tie	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Flammability	UL 94 HB

UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-00408](#)