

Specification Sheet

Part Number: 156-01092

The 360 degree locking enclosure and cable tie dynamically fit a range of bundle sizes.

Clamp can be opened for bundle maintenance.

Low-profile release tab won't interfere with bundle or nearby routing.

The two bundles are allowed to rotate up to 90 degrees from one another.



LOC Locking Clamp, 10 - 14 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 3000/ctn

Article Number	156-01092
----------------	-----------

Type	T50RLOC10-14-SET
------	------------------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	HellermannTyton's two-piece cable tie assembly offers dual bundle routing. The clip portion creates a full and secure lock completely around one bundle, while the cable tie creates a secure solution for a second bundle.
---------------------	---

Short Description	LOC Locking Clamp, 10 - 14 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 3000/ctn
-------------------	--

Global Part Name	T50RLOC10-14-SET-PA66HS/PA66HIRHSUV-BK
------------------	--

Contents of pkg/kit	5000 T50R + 5000 LOC10-14
---------------------	---------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	1.09
---------------------	------

Length L (Metric)	27.6
-------------------	------

Fixation Method	Omega Clip
-----------------	------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.47
--------------------	------

Width W (Metric)	12.0
------------------	------

Bundle Diameter Min (Imperial)	0.39
--------------------------------	------

Bundle Diameter Min (Metric)	10.0
------------------------------	------

Bundle Diameter Max (Imperial)	0.55
--------------------------------	------

Bundle Diameter Max (Metric)	14.0
Height H (Imperial)	1.08
Height H (Metric)	27.4
Depth D (Imperial)	0.47
Depth D (Metric)	12.0
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV PA66HS
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	3000

Package Quantity (Metric)	3000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-01092](#)