

Specification Sheet

Part Number: 156-01349



Bundle can rotate to any orientation, allowing routing in any direction regardless of mounting point.
Clip is reusable, making relocation or adjustments simple.
All-in-one bundling and mounting solution reduces costs.

Wire and Swivel Clip Tie, 50lb, Diameter .15"-.17", 6.0" Long, PA66HS/PP, Black, 500/pkg

Article Number	156-01349
Type	T50SVC4S
Color	Black (BK)
Quantity Per	bag
Product Description	HellermannTyton’s 1-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners.
Short Description	Wire and Swivel Clip Tie, 50lb, Diameter .15"-.17", 6.0" Long, PA66HS/PP, Black, 500/pkg

Global Part Name	T50SVC4S-PA66HS/PP-BK
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	222
Length L (Imperial)	6.1
Length L (Metric)	155.0
Fixation Method	Omega Clips
Identification Plate Position	none
Width W (Imperial)	0.19
Width W (Metric)	4.7
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0
Bundle Diameter Max (Imperial)	1.4
Bundle Diameter Max (Metric)	35.0
Material	Polypropylene (PP) Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut	PP PA66HS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-01349](#)