

Specification Sheet

Part Number: 156-02110



Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement. Controlled flex and angled entry promote easy installation.

Independent rotation allows for adjustable routing orientation.

MOC Clip to MOC Clip Perpendicular, 14 mm, 14 mm Perpendicular, PA66HIRHSUV, Black, 2000/ctn

Article Number	156-02110
-----------------------	-----------

Type	MOC14FMOC14M180
-------------	-----------------

Color	Black (BK)
--------------	------------

Quantity Per	carton
---------------------	--------

Product Description	The MOC to MOC 180 is a rotatable dual routing clip that keeps two routings secured and separated. One clip is oriented 90 degrees from the other to provide alternative access for bundle attachment. A swivel coupler allows them to rotate independently of each other.
----------------------------	--

Short Description	MOC Clip to MOC Clip Perpendicular, 14 mm, 14 mm Perpendicular, PA66HIRHSUV, Black, 2000/ctn
--------------------------	--

Global Part Name	MOC14FMOC14M180-PA66HIRHSUV-BK
-------------------------	--------------------------------

Length L (Imperial)	1.93
Length L (Metric)	48.95
Variant	Clip to Clip Transverse
Bundle Diameter Min (Imperial)	0.51
Bundle Diameter Min (Metric)	13.0
Bundle Diameter Max (Imperial)	0.62
Bundle Diameter Max (Metric)	15.8
Height H (Imperial)	0.94
Height H (Metric)	23.8
Depth D (Imperial)	0.39
Depth D (Metric)	10.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB

Halogen Free	Yes
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-02110](#)