

Specification Sheet

Part Number: 156-02266



Bi-directional saddle allows for the securing of bundles perpendicular or parallel to mounting hole.
HellermannTyton's 4x oval prevents bundle rotation while providing best-in-class installation and extraction resistance for four common oval sizes.

2-Piece Cable Tie/Fir Tree Mount, Unassembled Set, 110mm Max Bundle, PA66HIRHSUV, Black, 3000/ctn

Article Number	156-02266
Type	T50LSADFTOVAL-SET
Color	Black (BK)
Quantity Per	carton
Product Description	These two-piece fasteners offer a simple and versatile method of bundling and mounting cables up to 4.3" (110 mm) to a panel up to 6.0 mm thick using an oval hole. The fir tree will easily push into pre-punched holes in panels or threaded blind holes and offers a secure fit. The two-piece design enables the head of the tie to be oriented in the required position to ease assembly, while the disc on top of the fir tree covers the hole and minimizes the ingress of water and dirt.

Short Description	2-Piece Cable Tie/Fir Tree Mount, Unassembled Set, 110mm Max Bundle, PA66HIRHSUV, Black, 3000/ctn
Global Part Name	T50LSADFTOVAL-SET-PA66HS/PA66HIRHS-BK
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225.0
Length L (Imperial)	15.0
Length L (Metric)	381.0
Fixation Method	Fir Tree for oval holes
Identification Plate Position	none
Tie Closure	plastic pawl
Width W (Imperial)	0.694
Width W (Metric)	17.63
Bundle Diameter Min (Imperial)	0.197
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	4.33
Bundle Diameter Max (Metric)	110.0

Height H (Imperial)	0.787
Height H (Metric)	20
Mounting Hole Diameter D (Imperial)	0.24 " X 0.48 " 0.26 " X 0.49 " 0.25 " X 0.51" 0.28 " X 0.47
Mounting Hole Diameter D (Metric)	7.0 x 12.0 mm 6.5 x 12.5 mm 6.5 x 13.0 mm 6.2 x 12.2 mm
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HIRHS PA66HS
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-02266](#)