

Specification Sheet

Part Number: 156-02434



Versatile and robust fir tree design provides low insertion effort yet delivers exceptional retention strength in an 6.5 mm hole and M8 threaded hole.

Wider and thinner strap design increases flexibility and minimizes pinching of bundles, hoses and tubing.

PA46 nylon material provides great performance at up to 135°F continuous operating temperature.

2-Piece Cable Tie/Fir Tree Mount, 6.5mm Hole and M8 Threaded Hole, PA46, Brown, 1200/ctn

Article Number	156-02434
Type	WSSDFTM8WSSDSET
Color	Brown (BN)
Quantity Per	carton
Product Description	These two-piece fasteners are pre-assembled and offer a simple and versatile method of bundling and mounting cables. Sold as an unassembled set, this oval fir tree and tie combination allows the user to install the tie in two different directions, securing the bundle perpendicular or inline to the oval mounting hole.
Short Description	2-Piece Cable Tie/Fir Tree Mount, 6.5mm Hole and M8 Threaded Hole, PA46, Brown, 1200/ctn

Global Part Name	WSSDFTM8WSSDSET-PA46-BN
------------------	-------------------------

Minimum Tensile Strength (Imperial)	120.0
-------------------------------------	-------

Minimum Tensile Strength (Metric)	533.0
-----------------------------------	-------

Length L (Imperial)	9.1
---------------------	-----

Length L (Metric)	231.14
-------------------	--------

Fixation Method	Fir Tree
-----------------	----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.88
--------------------	------

Width W (Metric)	22.6
------------------	------

Bundle Diameter Min (Imperial)	0.37
--------------------------------	------

Bundle Diameter Min (Metric)	9.4
------------------------------	-----

Bundle Diameter Max (Imperial)	2.25
--------------------------------	------

Bundle Diameter Max (Metric)	57.15
------------------------------	-------

Height H (Imperial)	0.89
Height H (Metric)	22.77
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.23
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.25
Mounting Hole Diameter D (Metric)	M8 6.5 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.27

Material	Polyamide 4.6 (PA46)
Material Shortcut	PA46
Flammability	UL 94 V-2
Halogen Free	Yes
Operating Temperature	-40°F to +266°F (-40°C to +130°C)

Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	1200
Package Quantity (Metric)	1200
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-02434](#)