

Specification Sheet

Part Number: 156-02482



Anti-rotation pin eliminates movement of bundle when fastening bolt.

Heavy duty mount with robust 120 lb tie delivers an ultra strong alternative to metal clamps.

Assembly withstands vibrations and displacement forces.

Metal bushing accommodates high tightening torque.

2-Piece Cable Tie/Screw Mount, Unassembled Set, 15" L, M8 Hole, 120lb, PA66HIRHS, Black, 1000/ctn

Article Number 156-02482

Type T120RCPCM8-TSSET

Color Black (BK)

Quantity Per carton

Product Description These heavy duty cable tie mounts, secured with mechanical fasteners, include an anti-rotation pin that keeps the mount and harness assembly in position during the torquing of the bolt or nut. They provide an attachment point for securing and routing a single bundle. The mounts provide the highest level of fastening for critical cable security.

Short Description 2-Piece Cable Tie/Screw Mount, Unassembled Set, 15" L, M8 Hole, 120lb, PA66HIRHS, Black, 1000/ctn

Global Part Name	T120RCPCM8-TSSET-PA66HIRHSUV/PA66HIRHS-BK
------------------	---

Minimum Tensile Strength (Imperial)	120
-------------------------------------	-----

Minimum Tensile Strength (Metric)	535
-----------------------------------	-----

Length L (Imperial)	15.0
---------------------	------

Length L (Metric)	385.0
-------------------	-------

Fixation Method	Screw Mount
-----------------	-------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.30
--------------------	------

Width W (Metric)	7.6
------------------	-----

Bundle Diameter Min (Imperial)	0.20
--------------------------------	------

Bundle Diameter Min (Metric)	5.0
------------------------------	-----

Bundle Diameter Max (Imperial)	4.13
--------------------------------	------

Bundle Diameter Max (Metric)	105.0
------------------------------	-------

Thickness T (Imperial)	0.07
------------------------	------

Thickness T (Metric)	1.8
Height H (Imperial)	0.92
Height H (Metric)	23.5
Mounting Hole Diameter D (Imperial)	0.33
Mounting Hole Diameter D (Metric)	8.4 mm
Mounting Hole Diameter D Max (Metric)	8.5
Stud Diameter (Metric)	8.0 mm
Stud Diameter (Imperial)	0.31
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHS PA66HIRHSUV
Material Cable Tie	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +230°F (-40°C to +110°C)

ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-02482](#)