

Specification Sheet

Part Number: 156-02586



Cable tie and weld stud mounting base are supplied pre-assembled for ease and speed of installation

Mount features a "soft-push" design - no tools required to fit the parts to the stud

M5/T5/M6/T6 Stud Mount Tie 7.95" L, 50lb Tensile, PA66HIRHS, Black, 100/pkg

Article Number	156-02586
-----------------------	-----------

Type	T50R0SBS5-6U
-------------	--------------

Color	Black (BK)
--------------	------------

Quantity Per	bag
---------------------	-----

Product Description	Unique, two-piece design allows routing to be above, parallel or perpendicular to stud. This also enables up to three separate bundles to be fastened to the same stud. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.
----------------------------	--

Short Description	M5/T5/M6/T6 Stud Mount Tie 7.95" L, 50lb Tensile, PA66HIRHS, Black, 100/pkg
--------------------------	---

Global Part Name	T50R0SBS5-6U-PA66HS/PA66HIRHS-BK
------------------	----------------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	200
-----------------------------------	-----

Length L (Imperial)	7.95
---------------------	------

Length L (Metric)	202.0
-------------------	-------

Fixation Method	Weld Stud Fixing
-----------------	------------------

Identification Plate Position	none
-------------------------------	------

Tie Closure	plastic pawl
-------------	--------------

Width W (Imperial)	0.18
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.16
--------------------------------	------

Bundle Diameter Min (Metric)	4.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.97
--------------------------------	------

Bundle Diameter Max (Metric)	50.0
------------------------------	------

Height H (Imperial)	0.05
---------------------	------

Height H (Metric)	1.2
-------------------	-----

Stud Diameter (Metric)	M5 M6
Stud Diameter (Imperial)	0.20
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS PA66HS
Flammability	UL 94 HB
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-02586](#)