

Specification Sheet

Part Number: 156-02592

Robust fir tree design provides low insertion effort yet delivers exceptional retention strength in a 12 mm hole, for ease of use and reliable performance.

Heavy Duty T120 tie provides a 120lb (534 N) tensile strength to secure bundles up to 4" (104 mm).

Friction tab inside the fir tree allows the tie to sit in mount without falling out prior to installation.

PA46 nylon material provides great performance at up to 135°F continuous operating temperature.



2-Piece Cable Tie/Fir Tree Mount, Unassembled Set, 15.2"L, 12mm Mounting Hole, PA46, Gray, 1000/ctn

Article Number	156-02592
-----------------------	-----------

Type	T120RFT12SET
-------------	--------------

Color	Gray (GY)
--------------	-----------

Quantity Per	carton
---------------------	--------

Product Description	These two-piece fasteners offer a simple and versatile method of bundling and mounting cables. Sold as an unassembled set, this oval fir tree and tie combination allows the user to install the tie in two different directions, securing the bundle perpendicular or inline to the oval mounting hole.
----------------------------	--

Short Description	2-Piece Cable Tie/Fir Tree Mount, Unassembled Set, 15.2"L, 12mm Mounting Hole, PA46, Gray, 1000/ctn
Global Part Name	T120RFT12SET-PA46-GY
Minimum Tensile Strength (Imperial)	120.0
Minimum Tensile Strength (Metric)	535.0
Length L (Imperial)	0.89
Length L (Metric)	22.6
Fixation Method	Fir Tree
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.80
Width W (Metric)	20.40
Bundle Diameter Min (Imperial)	0.20
Bundle Diameter Min (Metric)	5.0

Bundle Diameter Max (Imperial)	4.13
Bundle Diameter Max (Metric)	105.0
Height H (Imperial)	1.17
Height H (Metric)	29.70
Mounting Hole Diameter D (Imperial)	0.47
Mounting Hole Diameter D (Metric)	12.0 mm
Material	Polyamide 4.6 (PA46)
Material Shortcut	PA46
Operating Temperature	-40°F to +266°F (-40°C to +130°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-02592](#)