

Specification Sheet

Part Number: 157-00236



One piece cable tie and fixing offers a simple and easy to use method of bundling and fixing cables.

The design of the fir tree ensures a positive and secure fixing into panels with thicknesses from 0.6mm to 6.0mm or threaded blind holes.

Disc on the top of the fir tree covers the hole and minimizes the ingress of water and dirt.

1-Pc Cable Tie/Fir Tree Mount, 6.0" Long, 21" Mounting Hole, PA66HIRHSUV, Black, 1000/pkg

Article Number	157-00236
Type	T50SOSFT5.35
Color	Black (BK)
Quantity Per	bag
Product Description	Fir tree mounts with ties cables provide a secure grip in mounting holes and protect against dirt and other impurities. The mount provides low insertion and high extraction force.
Short Description	1-Pc Cable Tie/Fir Tree Mount, 6.0" Long, 21" Mounting Hole, PA66HIRHSUV, Black, 1000/pkg
Global Part Name	T50SOSFT5.35-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)	40.0
Minimum Tensile Strength (Metric)	180.0
Length L (Imperial)	6.4
Length L (Metric)	163.0
Fixation Method	Fir Tree
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	35.0
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.3

Panel Thickness Min (Imperial)	.02
Panel Thickness Max (Imperial)	0.23
Panel Thickness Min (Metric)	0.60
Panel Thickness Max (Metric)	6.00
Mounting Hole Diameter D (Imperial)	0.20 - 0.22
Mounting Hole Diameter D (Metric)	5.35 mm
Mounting Hole Diameter D Min (Imperial)	0.2
Mounting Hole Diameter D Max (Imperial)	0.22
Mounting Hole Diameter D Max (Metric)	5.6
Disc Diameter (Metric)	16.3
Disc Diameter (Imperial)	0.64
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 V-2
Operating Temperature	-40°F to +221°F (-40°C to +105°C)

ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[157-00236](#)