

Specification Sheet

Part Number: 157-00268



One-piece bundling and fastening solution reduces costs and assembly time.

Low-profile fir tree avoids obstructions on the opposite side of the panel.

HellermannTyton's 4x oval prevents bundle rotation while providing best-in-class installation ergonomics and extraction resistance for four common oval sizes.

The fir tree branch design on all four sides makes a 360-degree interface with the panel, creating a more secure fit into the hole.

Disc feature prevents rattling in high-vibration applications and protects against debris ingress.

1-Pc Cable Tie/Fir Tree Mount with Disc, 8.5"L, 6.2 - 13.0 mm, PA66HIRHSUV, Black 1000/bag

Article Number	157-00268
Type	T50ROSFTSOVAL
Color	Black (BK)
Quantity Per	bag

Product Description	One-piece cable tie and mount offers a simple bundling and mounting solution. The innovative design of this fir tree establishes a 360-degree interface with the panel hole, ensuring a more secure fit. The oval shape won't rotate once inserted, ensuring proper routing of wires and hoses. The disc feature prevents rattling in high-vibration applications and protects against debris ingress.		
Short Description	1-Pc Cable Tie/Fir Tree Mount with Disc, 8.5"L, 6.2 - 13.0 mm, PA66HIRHSUV, Black 1000/bag		
Global Part Name	T50ROSFTSOVAL-PA66HIRHSUV-BK		
Minimum Tensile Strength (Imperial)	50.0		
Minimum Tensile Strength (Metric)	225.0		
Length L (Imperial)	8.5		
Length L (Metric)	215.9		
Fixation Method	Fir Tree for oval holes		
Identification Plate Position	none		
Releasable Closure	No		
Tie Closure	plastic pawl		
Variant	Outside Serrated		
Width W (Imperial)	0.18		
Width W (Metric)	4.70		

Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Height H (Imperial)	0.32
Height H (Metric)	8.05
Panel Thickness Min (Imperial)	0.023
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.24 x 0.48 ";0.25 x 0.50 ";0.25 x 0.51 ";0.27 x 0.47
Mounting Hole Diameter D (Metric)	6.2 x 12.2 mm 7.0 x 12.0 mm 6.5 x 12.5 mm 6.5 x 13.0 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.51
Mounting Hole Diameter D Max (Metric)	13.0
Disc Diameter (Metric)	17.6 x 23.6
Disc Diameter (Imperial)	0.69 x 0.93

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[157-00268](#)