

Specification Sheet

Part Number: 157-00400

Mount provides low insertion and high extraction forces which makes for a strong and easy installation.

Tie utilizes a strong hinge between the stud mount and strap head to provide superior holding ability.

Clamping rails increase grip on round bundles.

Thinner strap provides increased flexibility for improved ergonomics.



Wide Strap Cable Tie with .25" Stud Mount, 9.7" Long, 0.5" Wide, PA66HIRHSUV, Black, 300/bg

Article Number	157-00400
----------------	-----------

Type	WSS250
------	--------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	The Wide Strap Stud Mount Cable Tie minimizes pinching on soft bundles and features a low profile head to provide compact bundling. A thinner strap provides increased flexibility for improved ergonomics. Available in various stud mount sizes, the wide strap tie utilizes a strong hinge between the stud mount and head to provide superior holding ability on a threaded stud.
---------------------	--

Short Description	Wide Strap Cable Tie with .25" Stud Mount, 9.7" Long, 0.5" Wide, PA66HIRHSUV, Black, 300/bg
Global Part Name	WSS250-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	120
Minimum Tensile Strength (Metric)	535
Length L (Imperial)	9.7
Length L (Metric)	246.4
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.5
Width W (Metric)	12.7
Bundle Diameter Min (Imperial)	0.38
Bundle Diameter Min (Metric)	9.5
Bundle Diameter Max (Imperial)	2.25

Bundle Diameter Max (Metric)	57.1
Stud Diameter (Metric)	M6
Stud Diamater (Imperial)	1/4
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	300
Package Quantity (Metric)	300
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[157-00400](#)