

Specification Sheet

Part Number: 161-63503

Designed for applications that demand high flame retardant materials

Unique open design allows for easy branch-offs at any point along the harness

Overwrap formation provides abrasion protection and accommodates multiple bundle configurations

Flexible construction and design is well suited for applications that involve movement and vibration

Easy-to-use installation tool makes assembly fast and easy



Helawrap, HWPAV030, 1-1/4" (30mm) Dia, PA6V0, Black, 100 ft/reel

Article Number	161-63503
----------------	-----------

Type	HWPAV030
------	----------

Color	Black (BK)
-------	------------

Quantity Per	reel
--------------	------

Product Description	The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Helawrap easily wraps around cables with a "zipper-like" motion to protect against abrasion and mechanical stress caused by movement and bending. A handy application tool is included in every package for faster installations.
---------------------	---

Short Description	Helawrap, HWPAV030, 1-1/4" (30mm) Dia, PA6V0, Black, 100 ft/reel
Global Part Name	HWPAV030-PA6V0-BK
Length L (Imperial)	100.0
Length L (Metric)	30.48
Variant	Spiral Binding
Bundle Diameter Min (Imperial)	1.14
Bundle Diameter Min (Metric)	29.0
Bundle Diameter Max (Imperial)	1.26
Bundle Diameter Max (Metric)	32.0
Diameter D (Imperial)	1.25
Diameter D (Metric)	30.0
Nominal Diameter (Imperial)	1.25
Nominal Diameter (Metric)	31.75
Wall Thickness WT (Imperial)	0.050
Wall Thickness WT (Metric)	1.30

Material	Polyamide 6 V0 (PA6V0)
Material Shortcut	PA6V0
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	EN [45545-2] UL UL 1441
UL Recognized (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global

customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin.
(www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[161-63503](#)