

Specification Sheet

Part Number: 166-90305



External NPT thread provides a secure connection.

Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.

All-around "teeth" attach firmly to conduit and deliver a high extraction force.

Durable nylon material has high resistance to salts, oils, weak acids and solvents.

IP66 fitting has one-piece construction.

HelaGuard Non-Metallic IP66 Fitting, Straight, 1/2" NPT Thread, 0.38" Dia, PA66, Black, 10/pkg

Article Number	166-90305
----------------	-----------

Type	HG038-S-0500
------	--------------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	HelaGuard Non-Metallic Straight fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. IP66 ingress protection rated fittings.
---------------------	--

Short Description	HelaGuard Non-Metallic IP66 Fitting, Straight, 1/2" NPT Thread, 0.38" Dia, PA66, Black, 10/pkg
Global Part Name	HG038-S-0500-PA66-BK
Length L (Imperial)	1.73
Length L (Metric)	44
Variant	Straight
Outside Diameter OD (Imperial)	1.14
Outside Diameter OD (Metric)	29
Nominal Diameter (Imperial)	0.38
Nominal Diameter (Metric)	16
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No

Operating Temperature	-58°F to +275°F (-50°C to +135°C)
-----------------------	-----------------------------------

Reach Compliant (Article 33)	Yes
------------------------------	-----

ROHS Compliant	Yes
----------------	-----

UL Recognized (US)	Yes
--------------------	-----

UL Recognized (US and Canada)	Yes
-------------------------------	-----

Package Quantity (Imperial)	10
-----------------------------	----

Package Quantity (Metric)	10
---------------------------	----

Customs Number	3926909988
----------------	------------

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[166-90305](#)