

## Specification Sheet

Part Number: 166-90321



External Metric thread provides a secure connection.

Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.

All-around "teeth" attach firmly to conduit and deliver a high extraction force.

Durable nylon material has high resistance to salts, oils, weak acids and solvents.

IP66 fitting has one-piece construction.

HelaGuard Non-Metallic IP66 Fitting, Straight, M20 Thread, 0.38" Dia, PA66, Black, 10/pkg

**Article Number** 166-90321

**Type** HG038-S-M20

**Color** Black (BK)

**Quantity Per** bag

**Product Description** HelaGuard Non-Metallic Straight fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. IP66 ingress protection rated fittings.

<b>Short Description</b>	HelaGuard Non-Metallic IP66 Fitting, Straight, M20 Thread, 0.38" Dia, PA66, Black, 10/pkg
<b>Global Part Name</b>	HG038-S-M20-PA66-BK
<b>Length L (Imperial)</b>	1.73
<b>Length L (Metric)</b>	44
<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Operating Temperature</b>	-58°F to +275°F (-50°C to +135°C)
<b>ROHS Compliant</b>	Yes
<b>Package Quantity (Imperial)</b>	10
<b>Package Quantity (Metric)</b>	10
<b>Customs Number</b>	3926909988



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[166-90321](#)