

Specification Sheet

Part Number: 166-90325

External Metric thread provides a secure connection.

Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.

All-around "teeth" attach firmly to conduit and deliver a high extraction force.

Durable nylon material has high resistance to salts, oils, weak acids and solvents.

IP66 fitting has one-piece construction.



HelaGuard Non-Metallic IP66 Fitting, Straight, M20 Thread, 0.50" Dia, PA66, Black, 10/pkg

Article Number 166-90325

Type HG050-S-M20

Color Black (BK)

Quantity Per bag

Product Description HelaGuard Non-Metallic Straight fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. IP66 ingress protection rated fittings.

Short Description	HelaGuard Non-Metallic IP66 Fitting, Straight, M20 Thread, 0.50" Dia, PA66, Black, 10/pkg
Global Part Name	HG050-S-M20-PA66-BK
Length L (Imperial)	1.73
Length L (Metric)	44
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[166-90325](#)