

Specification Sheet

Part Number: 166-90327

External Metric thread provides a secure connection.

Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.

All-around "teeth" attach firmly to conduit and deliver a high extraction force.

Durable nylon material has high resistance to salts, oils, weak acids and solvents.

IP66 fitting has one-piece construction.



HelaGuard Non-Metallic IP66 Fitting, Straight, M32 Thread, 1.00" Dia, PA66, Black, 10/pkg

Article Number 166-90327

Type HG100-S-M32

Color Black (BK)

Quantity Per bag

Product Description HelaGuard Non-Metallic Straight fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. IP66 ingress protection rated fittings.

| | |
|------------------------------------|---|
| Short Description | HelaGuard Non-Metallic IP66 Fitting, Straight, M32 Thread, 1.00" Dia, PA66, Black, 10/pkg |
| Global Part Name | HG100-S-M32-PA66-BK |
| Length L (Imperial) | 2.09 |
| Length L (Metric) | 53 |
| Material | Polyamide 6.6 (PA66) |
| Material Shortcut | PA66 |
| Operating Temperature | -58°F to +275°F (-50°C to +135°C) |
| ROHS Compliant | Yes |
| Package Quantity (Imperial) | 10 |
| Package Quantity (Metric) | 10 |
| Customs Number | 3926909988 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[166-90327](#)