

Specification Sheet

Part Number: FSU16-M20-C



Nickel plated brass compression fitting used with FSU, LFHU and FPU flexible metallic conduit.

Fitting includes elastomeric sealing washer for IP65 ingress protection.

Suitable for knockouts or NPT / Metric threaded entries as fitting rotates until tightened.

Metallic Compression Fitting, Straight, M20 Metric Thread, 3/8" (16mm) Dia, NPB Metal, 10/pkg

Article Number	166-90539
-----------------------	-----------

Type	FSU16-M20-C
-------------	-------------

Color	Metal (ML)
--------------	------------

Quantity Per	pack
---------------------	------

Product Description	Multipart straight compression fitting with fixed external thread pattern suitable for threaded or knockout entries. Constructed with nickel plated brass components that resist corrosion, ensures high mechanical strength and electrical continuity. Fitting comprised of body, nut, grounding ferrule and nylon compression seal. For use with FSU, FPU, and LFHU flexible metal conduits.
----------------------------	--

Short Description	Metallic Compression Fitting, Straight, M20 Metric Thread, 3/8" (16mm) Dia, NPB Metal, 10/pkg
--------------------------	---

Global Part Name	FSU16-M20-C-NPB/PA6-ML
Technical Description	Manufacturer Reference Number: FSU16-M20-C
Length L (Imperial)	1.3
Length L (Metric)	33.0
Variant	Straight
Height H (Imperial)	0.83
Height H (Metric)	24.0
Nominal Diameter (Imperial)	0.38
Nominal Diameter (Metric)	16.0
Material	Nickel Plated Brass (NPB) Polyamide 6 (PA6)
Material Shortcut	PA6 NPB
Halogen Free	Yes
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
-----------------------	-----

Package Quantity (Imperial)	10
------------------------------------	----

Package Quantity (Metric)	10
----------------------------------	----

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[FSU16-M20-C](#)