

Specification Sheet

Part Number: B-075-M25-EXD

Quickly converts thread size or style for use in threaded entries.
Obtain IP68 level ingress protection with use of sealing washer.

Suitable for use in Zone 1, Zone 2, Zone 21 and Zone 22 hazardous areas.

ATEX and IECEx EX d (Flameproof).

ATEX and IECEx EX e (Increased Safety).

ATEX and IECEx EX t (Dust Ignition Protection).



Hazardous Area Metallic Thread Converter, 3/4" NPT External/M25 Internal Thread, NPB Metal, 1/pkg

Article Number	166-90642
----------------	-----------

Type	B-075-M25-EXD
------	---------------

Color	Metal (ML)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Nickel plated brass thread converters used to increase, reduce or convert thread types in hazardous environments. For use with Flexicon's LTP-EXD fittings. Achieves IP68 level ingress protection with use of sealing washer.
---------------------	--

Short Description	Hazardous Area Metallic Thread Converter, 3/4" NPT External/M25 Internal Thread, NPB Metal, 1/pkg
-------------------	---

Global Part Name B-075-M25-EXD-NPB-ML

Technical Description Manufacturer Reference Number: B-075-M25--EXD

Variant Converter

Height H (Imperial) 1.28

Height H (Metric) 32.4

Nominal Diameter (Imperial) 0.75

Nominal Diameter (Metric) 25

Material Nickel Plated Brass (NPB)

Material Shortcut NPB

Operating Temperature -58°F to +275°F (-50°C to +135°C)

Package Quantity (Imperial) 1

Package Quantity (Metric) 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[B-075-M25-EXD](#)