

Specification Sheet

Part Number: 166-90826



Integrated Sealing Technology creates a true, one-piece component that reduces installation time and provides error free installation.

Nickel plated brass metric thread provides a secure connection even under dynamic conditions.

Swivel thread feature minimizes cable twisting and provides strain relief.

All-around "teeth" attach firmly to corrugated conduit and deliver a high extraction force.

Fittings deliver IP68 ingress protection against moisture and dirt.

HelaGuard NM 21mm IP68 Ultra Fitting, 90-Elbow Brass Swivel, Ext M20 Thread, NPB, PA66, Black, 10/pkg

Article Number	166-90826
----------------	-----------

Type	HGU21-90M-M20B
------	----------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Straight snap-on style fittings with nickel plated brass metric threaded fitting provides a true, one-piece component solution; seals are integrated into the fitting body. Durable nylon materials deliver high chemical resistance against salts, oils, weak acids and solvents. Designed for fast assembly and easy removal using a small screwdriver.
---------------------	---

Short Description	HelaGuard NM 21mm IP68 Ultra Fitting, 90-Elbow Brass Swivel, Ext M20 Thread, NPB, PA66, Black, 10/pkg
Global Part Name	HGU21-90M-M20B-NPB/PA66-BK
Length L (Imperial)	2.60
Length L (Metric)	66
Variant	90° Elbow
Nominal Diameter (Imperial)	0.5
Nominal Diameter (Metric)	21
Material	Nickel Plated Brass (NPB) Polyamide 6.6 (PA66)
Material Shortcut	NPB PA66
Flammability	Self-extinguishing
Halogen Free	Yes
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
ROHS Compliant	Yes

Package Quantity (Imperial)	10
------------------------------------	----

Package Quantity (Metric)	10
----------------------------------	----

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[166-90826](#)