

Specification Sheet

Part Number: 166-90849

External Metric thread provides a secure connection.

Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.

All-around "teeth" attach firmly to conduit and deliver a high extraction force.

Durable nylon material has high resistance to salts, oils, weak acids and solvents.

IP68 fitting has additional conduit seal for increased protection against wind, dirt, and water.



HelaGuard Non-Metallic IP68 Fitting, Straight, M20 Thread, 0.50" Dia, PA66, Black, 10/pkg

Article Number	166-90849
----------------	-----------

Type	HGL050-S-M20
------	--------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	<p>HelaGuard Non-Metallic Straight Swivel Flange fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. IP68 ingress protection rated fittings.</p>
---------------------	---

Short Description	HelaGuard Non-Metallic IP68 Fitting, Straight, M20 Thread, 0.50" Dia, PA66, Black, 10/pkg
Global Part Name	HGL050-S-M20-PA66-BK
Length L (Imperial)	1.73
Length L (Metric)	44
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[166-90849](#)