

Specification Sheet

Part Number: CTN380STD



- Durable tubing provides protection of wire harness from friction, vibration, fraying and puncture.
- Tubing protects cables and wires against automotive fluids and vibration wear.
- Weather resistant material provides protection against water, snow, ice, and the effects of heat or cold.
- Nylon material is formulated to withstand high temperatures.
- Lateral slit allows fast and easy insertion of wires.

Convoluted Tubing, Slit, 0.38" Dia, PA6, Black with Gray Stripe, 1900ft/carton

Article Number	169-60015
Type	CTN380
Color	Black with Gray Stripe (BKSTGY)
Quantity Per	carton
Product Description	Convoluted tubing provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. It also can serve to protect valuable wiring circuits. HellermannTyton’s convoluted tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat or cold on cables and wires. Available in standard, bulk, and dispenser box packaging. Material is slit.

Short Description	Convuluted Tubing, Slit, 0.38" Dia, PA6, Black with Gray Stripe, 1900ft/carton
Global Part Name	CTN380-PA6-BK
Length L (Imperial)	1900.0
Length L (Metric)	579.1
Variant	Slit
Inner Diameter D (Imperial)	0.380
Inner Diameter D (Metric)	9.65
Diameter D (Imperial)	0.526
Diameter D (Metric)	13.36
Outside Diameter OD (Imperial)	0.526
Outside Diameter OD (Metric)	13.36
Nominal Diameter (Imperial)	0.38
Nominal Diameter (Metric)	9.65
Wall Thickness WT (Imperial)	0.005
Wall Thickness WT (Metric)	0.127

Material	Polyamide 6 (PA6)
Material Shortcut	PA6
Flammability	UL 94 HB
Halogen Free	No
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1900
Package Quantity (Metric)	579.12
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[CTN380STD](#)