

Specification Sheet

Part Number: CTN340STDUNSLIT



- Durable tubing provides protection of wire harness from friction, vibration, fraying and puncture
- Tubing protects cables and wires against automotive fluids, vibration wear
- Weather resistant material provides protection against water, snow, ice, and the effects of heat, cold, and sunlight
- Nylon material is formulated to withstand high temperatures

Convoluted Tubing, Unslit, 0.75" Dia, PA6, Black with Gray Stripe, 450 ft/ctn

Article Number	169-60030
Type	CTN340UNSLIT
Color	Black with Gray Stripe (BKSTGY)
Quantity Per	carton
Product Description	HellermannTyton's Convoluted Tubing, also known as Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.

Short Description	Convuluted Tubing, Unslit, 0.75" Dia, PA6, Black with Gray Stripe, 450 ft/ctn
Global Part Name	CTN340UNSLIT-PA6-BK
Length L (Imperial)	450.0
Length L (Metric)	137.2
Variant	Unslit
Inner Diameter D (Imperial)	0.759
Inner Diameter D (Metric)	19.28
Diameter D (Imperial)	0.989
Diameter D (Metric)	25.12
Outside Diameter OD (Imperial)	0.989
Outside Diameter OD (Metric)	25.12
Nominal Diameter (Imperial)	0.75
Nominal Diameter (Metric)	19.05
Wall Thickness WT (Imperial)	0.005
Wall Thickness WT (Metric)	0.127

Material	Polyamide 6 (PA6)
Material Shortcut	PA6
Flammability	UL 94 HB
Halogen Free	No
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	450
Package Quantity (Metric)	137.16

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[CTN340STDUNSLIT](#)