

Specification Sheet

Part Number: CTP1120STD

Split side is ideal for applications where braided tubing or spiral wrap may be difficult to install.

Tubing provides full coverage where spiral wrap or other coverings may not be suitable.

In harsh applications the tubing provides resistance to crushing, impact, and abrasion.

Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires.



Convoluted Tubing, Slit, 1.5" Dia, PE, Black, 150ft/carton

Article Number	169-60503
----------------	-----------

Type	CTP1120
------	---------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.
Short Description	Convoluted Tubing, Slit, 1.5" Dia, PE, Black, 150ft/carton
Global Part Name	CTP1120-PE-BK
Length L (Imperial)	150.0
Length L (Metric)	45.7
Variant	Slit
Inner Diameter D (Imperial)	1.647
Inner Diameter D (Metric)	41.83
Diameter D (Imperial)	1.947
Diameter D (Metric)	49.45
Outside Diameter OD (Imperial)	1.947
Outside Diameter OD (Metric)	49.45
Nominal Diameter (Imperial)	1.5

Nominal Diameter (Metric)	38.1
Wall Thickness WT (Imperial)	0.006
Wall Thickness WT (Metric)	0.152
Material	Polyethylene (PE)
Material Shortcut	PE
Flammability	Not Flame Retardant
Halogen Free	No
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	150
Package Quantity (Metric)	45.7
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[CTP1120STD](#)