

## Specification Sheet

Part Number: CTP340

Split side is ideal for applications where braided tubing or spiral wrap may be difficult to install.

Tubing provides full coverage where spiral wrap or other coverings may not be suitable.

In harsh applications the tubing provides resistance to crushing, impact, and abrasion.

Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires.



Convoluted Tubing, Slit, 0.75" Dia, PE, Black, 4200 ft/carton

Article Number	169-60512
----------------	-----------

Type	CTP340
------	--------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	<p>HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.</p>
Short Description	Convoluted Tubing, Slit, 0.75" Dia, PE, Black, 4200 ft/carton
Global Part Name	CTP340-PE-BK
Length L (Imperial)	4200.0
Length L (Metric)	1280.2
Variant	Slit
Inner Diameter D (Imperial)	0.759
Inner Diameter D (Metric)	19.28
Diameter D (Imperial)	0.989
Diameter D (Metric)	25.12
Outside Diameter OD (Imperial)	0.989
Outside Diameter OD (Metric)	25.12
Nominal Diameter (Imperial)	0.75

Nominal Diameter (Metric)	19.05
Wall Thickness WT (Imperial)	0.005
Wall Thickness WT (Metric)	0.127
Material	Polyethylene (PE)
Material Shortcut	PE
Flammability	Not Flame Retardant
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	4200
Package Quantity (Metric)	1280
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[CTP340](#)