

Specification Sheet

Part Number: 170-03082



Split wrap design needs no fasteners and installs quickly, saving assembly time and future accessibility without disassembly.

Bends to a tight radius without distortion or splitting open.

Unique construction retains shape and rigidity throughout unrolling.

Easy open design allows quick access and ability to apply protective sleeving post assembly or post installation situations.

Braided Sleeving, Split Wrap, 0.25" Dia, PET, Orange, 200 ft/bulk reel

Article Number	170-03082
Type	BSPSW143B
Color	Orange (OG), High Voltage (HV)
Quantity Per	box
Product Description	A lateral split semi-rigid braided sleeving configuration used when ease of installation and repeat access to wire bundle is required. The lateral split allows the sleeving to open and accommodate a variety of bundling requirements. The 25% edge overlap rolls back over connectors and splices without exposing the bundled wires.
Short Description	Braided Sleeving, Split Wrap, 0.25" Dia, PET, Orange, 200 ft/bulk reel

Global Part Name	BSPSW143B-PET-OG
------------------	------------------

Length L (Imperial)	200.0
---------------------	-------

Length L (Metric)	61.0
-------------------	------

Bundle Diameter Min (Imperial)	0.1
--------------------------------	-----

Bundle Diameter Min (Metric)	2.54
------------------------------	------

Bundle Diameter Max (Imperial)	0.25
--------------------------------	------

Bundle Diameter Max (Metric)	6.4
------------------------------	-----

Diameter D (Imperial)	0.25
-----------------------	------

Diameter D (Metric)	6.4
---------------------	-----

Nominal Diameter (Imperial)	0.25
-----------------------------	------

Nominal Diameter (Metric)	6.4
---------------------------	-----

Wall Thickness WT (Imperial)	0.025
------------------------------	-------

Wall Thickness WT (Metric)	0.64
----------------------------	------

Material	Polyester (PET)
----------	-----------------

Material Shortcut	PET
-------------------	-----

Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	200
Package Quantity (Metric)	60.96
Customs Number	5808100000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[170-03082](#)