

Specification Sheet

Part Number: 170-03143

Split wrap design installs quickly, saving assembly time and future accessibility without disassembly.

Unique construction retains shape and rigidity throughout operating temperature range.

Easy open design allows quick assembly, future access, and ability to apply protective sleeving post assembly or post installation situations.

Self wrapping design eliminates the need for fasteners.

Provides a greater flexibility than spiralwrap or convoluted tubing.



Braided Sleeving, Split Wrap, Flame Retardant, 0.75" Dia, PET, Black, 100 ft/bulk reel

Article Number	170-03143
Type	BSSWFR340B
Color	Black (BK)
Quantity Per	box

Product Description	Used when flame retardancy is a primary requirement, this protection option incorporates a lateral split which allows the tube to open up to accommodate a variety of bundling requirements. The semi-rigid braid configuration simply closes around the entire installation without the need for any additional fasteners. Split wrap flame retardant braided sleeving is self-extinguishing and complies with UL VW-1 standards where cables exit a wall and need to be managed for an uncluttered, clean appearance.
Short Description	Braided Sleeving, Split Wrap, Flame Retardant, 0.75" Dia, PET, Black, 100 ft/bulk reel
Global Part Name	BSSWFR340B-PET-BK
Length L (Imperial)	100.0
Length L (Metric)	30.48
Bundle Diameter Min (Imperial)	0.75
Bundle Diameter Min (Metric)	19.1
Bundle Diameter Max (Imperial)	0.75
Bundle Diameter Max (Metric)	19.1
Diameter D (Imperial)	0.75
Diameter D (Metric)	19.1
Nominal Diameter (Imperial)	0.75
Nominal Diameter (Metric)	19.1

Wall Thickness WT (Imperial)	0.025
Wall Thickness WT (Metric)	0.64
Material	Polyester (PET)
Material Shortcut	PET
Flammability	FAR 25 UL 224 VW-1
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	ASTM 1354 ASTM E 162 ASTM E 662
UL Recognized (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	5808100000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[170-03143](#)