

Specification Sheet

Part Number: 170-03214



Split wrap design installs quickly, saving assembly time and future accessibility without disassembly.
Unique construction retains shape and rigidity throughout unrolling.
Easy open design allows quick assembly, future access, and ability to apply protective sleeving post assembly or post installation situations.

Braided Sleeving, Split Wrap, 0.5" Dia, PET, Black, 10 ft/pkg

Article Number	170-03214
Type	BSPSW120
Color	Black (BK)
Quantity Per	pack
Product Description	A lateral split semi-rigid braided sleeving configuration used when ease of installation and repeat access to wire bundle is required. The lateral split allows the sleeving to open and accommodate a variety of bundling requirements. The 25% edge overlap rolls back over connectors and splices without exposing the bundled wires.
Short Description	Braided Sleeving, Split Wrap, 0.5" Dia, PET, Black, 10 ft/pkg
Global Part Name	BSPSW120-PET-BK

Length L (Imperial) 10.0

Length L (Metric) 3.05

Bundle Diameter Min (Imperial) 0.1

Bundle Diameter Min (Metric) 2.54

Bundle Diameter Max (Imperial) 0.5

Bundle Diameter Max (Metric) 12.7

Diameter D (Imperial) 0.5

Diameter D (Metric) 12.7

Nominal Diameter (Imperial) 0.5

Nominal Diameter (Metric) 12.7

Material Polyester (PET)

Material Shortcut PET

Flammability UL 94 V-0

Halogen Free Yes

Operating Temperature	-94°F to +257°F (-70°C to +125°C)
------------------------------	-----------------------------------

Reach Compliant (Article 33)	Yes
-------------------------------------	-----

ROHS Compliant	Yes
-----------------------	-----

UL Recognized (US)	Yes
---------------------------	-----

Package Quantity (Imperial)	10
------------------------------------	----

Package Quantity (Metric)	3.05
----------------------------------	------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[170-03214](#)