

Specification Sheet

Part Number: 181-00609



Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.

Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.

Mounting holes are uniform in size and are offered every 2 inches to accommodate compact designs and ease installation.

Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.

High Density Slotted Wall Wiring Duct, 2" x 3", Non-Adhesive, PVC, Black, 120ft/Carton

|                     |  |
|---------------------|--|
| Article Number      | 181-00609  |
| Type                | SLHD2X3  |
| Color               | Black (BK)   |
| Quantity Per        | carton   |
| Product Description | HellermannTyton High-Density Slotted Wall Wiring Duct features narrow fingers equaling a 2-to-1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated. |

|                                  |  |
|----------------------------------|--|
| Short Description                | High Density Slotted Wall Wiring Duct, 2" x 3", Non-Adhesive, PVC, Black, 120ft/Carton |
| Global Part Name                 | SLHD2X3-PVC-BK   |
| Length L (Imperial)              | 6.0  |
| Length L (Metric)                | 1.83   |
| Fixation Method                  | Non-Adhesive   |
| Width W (Imperial)               | 2.0  |
| Width W (Metric)                 | 50.8   |
| Height H (Imperial)              | 3.07   |
| Height H (Metric)                | 77.9   |
| Mounting Hole Centers (Imperial) | 2.0  |
| Material                         | Polyvinylchloride (PVC)  |
| Material Shortcut                | PVC  |
| Halogen Free                     | No   |
| UV Resistant (Yes/No)            | No   |

|                              |  |
|------------------------------|--|
| Operating Temperature        | +122°F (+50°C)                                   |
| Reach Compliant (Article 33) | No   |
| ROHS Compliant               | Yes  |
| Certification/Specification  | CSA EN 50085-2-3_1A UL EN 50085-1:2005 + A1:2013 |
| UL Recognized (US)           | Yes  |
| Package Quantity (Imperial)  | 120.0  |
| Package Quantity (Metric)    | 36.58  |
| Customs Number               | 3925900000                                       |

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[181-00609](#)