

Specification Sheet

Part Number: SLWR20C2



Retainer spans approximately 90% over the duct opening for effective wire management.

Wire Retainer, Slotted Style for 2" Duct, Black, PA66, 100/bg

Article Number	181-20021
Type	SLWR20
Color	Black (BK)
Quantity Per	bag
Product Description	Slotted wall wire retainers snap in from the outside of the duct, allowing for fast and easy installation and removal. Slotted wall wire retainers are manufactured from black nylon 6/6.
Short Description	Wire Retainer, Slotted Style for 2" Duct, Black, PA66, 100/bg
Global Part Name	SLWR20-PA66-BK

Length L (Metric)	1.83
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	+23°F to +176°F (-5°C to +80°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach

to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[SLWR20C2](#)