

Specification Sheet

Part Number: 181-32003



Solid wall construction provides excellent coverage to keep wires clean. Durable material protects wires from damage, with long-lasting performance.

Available standard colors complement or contrast in light and dark environments.

Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.

Solid Wall Wiring Duct, 3" x 2", Non-Adhesive, PVC, White, 120ft/Carton

| | |
|---------------------|---|
| Article Number | 181-32003 |
| Type | SD3X2 |
| Color | White (WH) |
| Quantity Per | carton |
| Product Description | HellermannTyton Solid Wall Wiring Duct efficiently routes and protects wire. Solid wall wiring duct is designed for straight wire runs where breakouts are not required. Solid wall wiring duct is manufactured from high-impact, rigid PVC; comes in standard colors of white, gray and black; and is available in 6-foot lengths. |
| Short Description | Solid Wall Wiring Duct, 3" x 2", Non-Adhesive, PVC, White, 120ft/Carton |

| | |
|------------------|--------------|
| Global Part Name | SD3X2-PVC-WH |
|------------------|--------------|

| | |
|---------------------|-----|
| Length L (Imperial) | 6.0 |
|---------------------|-----|

| | |
|-------------------|------|
| Length L (Metric) | 1.83 |
|-------------------|------|

| | |
|-----------------|--------------|
| Fixation Method | Non-Adhesive |
|-----------------|--------------|

| | |
|--------------------|-----|
| Width W (Imperial) | 3.0 |
|--------------------|-----|

| | |
|------------------|------|
| Width W (Metric) | 76.2 |
|------------------|------|

| | |
|---------------------|------|
| Height H (Imperial) | 2.07 |
|---------------------|------|

| | |
|-------------------|------|
| Height H (Metric) | 52.6 |
|-------------------|------|

| | |
|----------------------------------|-----|
| Mounting Hole Centers (Imperial) | 4.0 |
|----------------------------------|-----|

| | |
|----------|-------------------------|
| Material | Polyvinylchloride (PVC) |
|----------|-------------------------|

| | |
|-------------------|-----|
| Material Shortcut | PVC |
|-------------------|-----|

| | |
|--------------|----|
| Halogen Free | No |
|--------------|----|

| | |
|-----------------------|----|
| UV Resistant (Yes/No) | No |
|-----------------------|----|

| | |
|-----------------------|----------------|
| Operating Temperature | +122°F (+50°C) |
|-----------------------|----------------|

| | |
|------------------------------|----|
| Reach Compliant (Article 33) | No |
|------------------------------|----|

| | |
|-----------------------------|--|
| ROHS Compliant | Yes |
| Certification/Specification | EN 50085-2-3_1A UL EN 50085-1:2005 + A1:2013 CSA |
| UL Recognized (US) | Yes |
| Package Quantity (Imperial) | 120.0 |
| Package Quantity (Metric) | 36.58 |
| Customs Number | 3925900000 |

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[181-32003](#)